Pillow-Shaped Liners

When filled, these industrial tote liners form the shape of a pillow. Pillow-shaped liners are typically constructed with two or three plies of linear low-density polyethylene (LLDPE) and a barrier film when used for aseptic and oxygen-barrier applications.



Benefits

- Manufactured in a clean environment, using cuttingedge CDF1 Smart Seal Technology™ that monitors and ensures consistent, high quality seals
- Ensures the absolute purity of your product
- Reduces foaming in bottom-filling applications
- Provides versatility; the same size bag fits many container sizes
- Provides excellent value for a wide range of liquid applications: bottom-fill applications and automated aseptic fillers
- CDF offers a variety of films, fitments and fitment placements





Pillow-Shape Liners

CDF1 Smart Seal Technology™

Using state-of-the-art equipment and quality control standards of the highest caliber, CDFl Smart Seal Technology™ ensures the ultimate reliability of IBC pillow liners. Proprietary CDFl Smart Seal Technology optimizes precision and consistency through monitoring the temperature, time and pressure of every seal on every liner.

Multiple Sizes

Pillow-shaped industrial tote liners are available in the following sizes. Other sizes are available by request.

38" x 56" 55 gallons

81" x 81" 275 gallons, recommended

for standard wood bins

used in the aseptic tomato and

juice industries

81" x 85" 275 gallons/300 gallons aseptic,

recommended for a standard wood bin tote or plastic IBC tote

.....

85" x 89" 330 gallons

90" x 90" 330 gallons

81" x 92" 350 gallons

95" x 95" over 350 gallons

Multiple Fitment Choices

CDF fitments are available in a variety of sizes.

Material Choices

All liners are made in America. The inside layer is made from FDA-approved films.

Barria™ metallized polyester is for oxygen and water vapor barrier.

Flexus™ and Flexus HF metallocene LLDPE are for general use, durability and flex crack resistance.

The film materials used in the manufacture of our IBC liners comply with FDA Regulations 21 CFR 177.1520, CFR 175.105, 177.1390 and CFR 177.1630.

We guarantee that our liners will be constructed from the specified materials and that CDF will not knowingly use materials that are out of specification or could be adulterated. No additives are introduced during the heat-sealing process.

Custom Designs

CDF will always consider custom designs.

Most Popular Product

• 7-1097



CDF Corporation, 77 Industrial Park Road, Plymouth, MA 02360 | ©2022 CDF Corporation | 0222

CDF warrants that its products will be free from defects in material and workmanship for one-hundred eighty (180) days after the date of delivery. Warranty claims must be made in writing no later than five (5) business days after the expiration of the warranty period. CDF's obligations under this warranty are limited solely to replacement of such products as are proven to be defective after CDF's inspection. Prior to use, the user shall independently determine the suitability of the products for the user's intended use and user assumes all risk and liability whatsoever in connection therewith. CDF products are intended for single use application. Any reuse of the liner and/or fitment voids this warranty.